

CTN 25 D5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, 10mm ² , 25mm ² , Hexagonal crimp
Order No.	9006230000
Type	CTN 25 D5
GTIN (EAN)	4008 190198459
Qty.	1 pc(s).

Creation date December 23, 2022 11:12:12 AM CET

Catalogue status 16.12.2022 / We reserve the right to make technical changes.

CTN 25 D5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	645.78 g		

Technical data

Description of article	Crimping tool for non-insulated connectors, 10-25 mm ² (tubular cable lug)	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 4	Conductor cross-section, min. AWG	AWG 8
Crimping range, max.	25 mm ²	Crimping range, min.	10 mm ²
Type of contact	Uninsulated connection		

tool data crimping

Crimping profile 1, min.	10 mm ²	Crimping profile 2, min.	16 mm ²
Crimping profile 3, min.	25 mm ²	Crimping type/profile	Hexagonal crimp

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Approvals

Approvals



Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

CTN 25 D5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

