

SAK Series
AP SAKK4/10 KER/WS**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Product image**

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	AP SAKK4/10 KER/WS
Order No.	9502630000
Version	SAK Series, End plate, 3 mm, white
GTIN (EAN)	4008 190047290
Qty.	10 pc(s).

SAK Series
AP SAKK4/10 KER/WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	3 mm	Width (inches)	0.118 inch
Height	40 mm	Height (inches)	1.575 inch
Depth	37 mm	Depth (inches)	1.457 inch
Net weight	14.3 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	250 °C		

Material data

Material	Ceramic	Colour	white
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Snap-on	Yes
---------	-----

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.1	27-14-11-33	eClass 10.0	27-14-11-33
UNSPSC	30-21-18-27		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks