

WK IK PH1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Delivery status	Discontinued
Available until	2017-12-31
Type	WK IK PH1
Order No.	9918470000
Version	Screwdriver insert, 200 mm, 1
GTIN (EAN)	4032248388837
Qty.	1 pc(s).
Alternative product	2433210000

WK IK PH1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	23 g	Net weight	33 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Screwing tools

Blade length	200 mm	Blade size, crosshead	1
Form	Philips	Size	1

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001509
ETIM 5.0	EC001509	ETIM 6.0	EC002115
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 6 TOOLS 15/16 EN
--------------------	--