

FS 2CO F ECO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|---------------|-------------------------------------|
| Order No. | 1190740000 |
| Type | FS 2CO F ECO |
| GTIN (EAN) | 4032248984046 |
| Qty. | 10 items |
| Local product | Only available in certain countries |

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E355547

General ordering data

Local product Only available in certain countries

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 30 mm | Depth (inches) | 1.1811 inch |
| Height | 75 mm | Height (inches) | 2.9527 inch |
| Width | 22 mm | Width (inches) | 0.8661 inch |
| Net weight | 37 g | | |

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus) E355547

Load side

Rated switching voltage 300 V AC Max. switching voltage, AC 300 V

General data

Version Flat design

Further details of approvals / standards

Certificate No. (cURus) E355547

Connection data

Wire connection method Screw connection

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001456 | ETIM 7.0 | EC001456 |
| ETIM 8.0 | EC001456 | ETIM 9.0 | EC001456 |
| ETIM 10.0 | EC001456 | ECLASS 9.0 | 27-37-16-03 |
| ECLASS 9.1 | 27-37-16-03 | ECLASS 10.0 | 27-37-16-03 |
| ECLASS 11.0 | 27-37-16-03 | ECLASS 12.0 | 27-37-16-03 |
| ECLASS 13.0 | 27-37-16-03 | ECLASS 14.0 | 27-37-16-03 |
| ECLASS 15.0 | 27-37-16-03 | | |