



### General ordering data

Order No.	1190750000
Type	<a href="#">FS 4CO F ECO</a>
GTIN (EAN)	4032248984053
Qty.	10 items
Local product	Only available in certain countries

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E355547

## General ordering data

Local product Only available in certain countries

## Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	29.5 mm	Width (inches)	1.1614 inch
Net weight	57 g		

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Rated data UL

Certificate No. (cURus) E355547

## Load side

Max. switching voltage, AC 250 V

## General data

Version Flat design

## Further details of approvals / standards

Certificate No. (cURus) E355547

## Connection data

Wire connection method Screw connection

## Classifications

ETIM 6.0	EC001456	ETIM 7.0	EC001456
ETIM 8.0	EC001456	ETIM 9.0	EC001456
ETIM 10.0	EC001456	ECLASS 9.0	27-37-16-03
ECLASS 9.1	27-37-16-03	ECLASS 10.0	27-37-16-03
ECLASS 11.0	27-37-16-03	ECLASS 12.0	27-37-16-03
ECLASS 13.0	27-37-16-03	ECLASS 14.0	27-37-16-03
ECLASS 15.0	27-37-16-03		