



Part Number : [1202550000](#)

Product Description : Contrinex Tester for Inductive and Photoelectric Sensors, Rechargeable with Universal Mobile Phone Charger, PNP, NPN, and Push-Pull Output Types

Series Number : 120255

Status : Active

Product Category : Sensor Accessories

Engineering Number : ATE-0000-010



Documents & Resources

Specifications

[1202550000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Sensor Accessories
Series	120255
Description	Contrinex Tester for Inductive and Photoelectric Sensors, Rechargeable with Universal Mobile Phone Charger, PNP, NPN, and Push-Pull Output Types
IP Rating	IP40
Product Name	Contrinex
Type	Inductive, Photoelectric
UPC	191130069347

Electrical

Current - Maximum Output	100 mA
Output	NPN, PNP, Push-Pull
Supply Voltage	24V DC

Physical

Accessory Type	Tester
Battery Life	>2 hours at 50 mA @ (600mAh)
Charger Type	Universal Mobile Phone Charger
Charging Time	< 5 hours @ (500 mA)
Housing Size	106 x 61mm
Output	NPN, PNP, Push-Pull
Rechargeable Battery Type	LiPo 9V 500 mAh