

**Clamping yoke
KLBUE 3-8 FM4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE 3-8 FM4
Order No.	1252530000
Version	Clamping yoke
GTIN (EAN)	4032248112531
Qty.	10 pc(s).

**Clamping yoke
KLBUE 3-8 FM4**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	14.5 mm	Width (inches)	0.571 inch
Height	50 mm	Height (inches)	1.969 inch
Depth	26 mm	Depth (inches)	1.024 inch
Net weight	17.2 g		

Material data

Colour	Silver
--------	--------

System specifications

Mounting rail	TS 35
---------------	-------

Additional technical data

Explosion-tested version	No
--------------------------	----

Conductors for clamping (rated connection)

Cable diameter, max.	8 mm	Cable diameter, min.	3 mm
----------------------	------	----------------------	------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC002020
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-90
eClass 8.1	27-14-11-50	eClass 9.0	27-14-11-50
eClass 9.1	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	Beipackzettel_KLBUE.pdf