

SH 4C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Bus bars offer the possibility to connect a large number of cables with a small footprint. In addition, integration into our terminal blocks for building installation is possible, or you can use our busbars to support the cable shield.

General ordering data

Version	Busbar support, silver, 85 °C, Width: 15 mm, None, Steel, galvanized, Direct mounting
Order No.	1340870000
Type	SH 4C
GTIN (EAN)	4050118208863
Qty.	10 pc(s).

SH 4C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	25 mm	Depth (inches)	0.984 inch
Height	25 mm	Height (inches)	0.984 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	24.388 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Operating temperature	-40 °C...85 °C
Continuous operating temp., max.	85 °C		

Material data

Material	Steel, galvanized	Colour	silver
UL 94 flammability rating	None		

Additional technical data

Installation advice	Direct mounting	Type of mounting	Direct mounting
---------------------	-----------------	------------------	-----------------

General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC001166	ETIM 7.0	EC001166
ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 9.0	27-40-06-07
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-40-06-07
ECLASS 11.0	27-40-06-07	ECLASS 12.0	27-40-06-07
ECLASS 13.0	27-40-06-07	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Engineering Data	CAD data – STEP CAD data – DWG CAD data – DXF
User Documentation	Beipackzettel_SH_4C.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format