


CB 98/2,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 2.5 x 98 mm, Polyamide 66, 80 N
Order No.	1697890000
Type	CB 98/2,5 BK
GTIN (EAN)	4008190882969
Qty.	100 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E317499

Dimensions and weights

Depth	1.1 mm	Depth (inches)	0.0433 inch
Height	98 mm	Height (inches)	3.8583 inch
Width	2.5 mm	Width (inches)	0.0984 inch
Net weight	0.26 g		

Temperatures

Operating temperature range -40...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	21 mm	Basic material	Polyamide 66
Tensile strength	80 N	Bundle diameter, max.	21 mm
Tensile strength (Pound-force)	18 lbf	Bundle diameter, min.	1 mm

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02
ECLASS 13.0	27-14-07-02	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

