

TS 35X7.5 2M/CRN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Stainless steel is a collective term for all types of steel (alloys) with a high degree of purity and corrosion resistance.

General ordering data

Version	Terminal rail, Accessories, Stainless steel 1.4301, untreated, Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	1747350000
Type	TS 35X7.5 2M/CRN
GTIN (EAN)	4032248003372
Qty.	40 M

TS 35X7.5 2M/CRN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	350 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Mounting rail

Installation advice	Direct mounting		
Standards	DIN EN 60715		
Surface finish	untreated		
Thickness	1.00 mm		
Basic material	Stainless steel 1.4301		
Length of the terminal rail	min.	0 mm	
	nominal	2000 mm	
	max.	2000 mm	
Pre-punched mounting rail	No		
Slit width			
Spacing of holes, centre-to-centre	0 mm		
Slit gap			
Slit length			

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

TS 35X7.5 2M/CRN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

