

**VP M40-MS65****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 40, 8 mm, Brass, nickel-plated
Order No.	<a href="#">177770000</a>
Type	VP M40-MS65
GTIN (EAN)	4032248158041
Qty.	50 items

## VP M40-MS65

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Height	13 mm	Height (inches)	0.5118 inch
Length	13 mm	Length (inches)	0.5118 inch
Diameter	44 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	7 mm	Net weight	33.5 g

### Temperatures

Operating temperature -40 °C... 100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

### General information

Head diameter	44.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Brass, nickel-plated
Diameter of sealing ring	40.00 mm	Sealing	NBR
External thread	M 40	Length of thread	8 mm

### Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-33	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05
ECLASS 13.0	27-14-08-05	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

