

**THM MULTIMARK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Version	Marking systems, Thermotransfer printer, Thermal transfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel
Order No.	<a href="#">2599430000</a>
Type	THM MULTIMARK
GTIN (EAN)	4050118626377
Qty.	1 items

**THM MULTIMARK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	253 mm	Depth (inches)	9.9606 inch
Height	320 mm	Height (inches)	12.5984 inch
Width	253 mm	Width (inches)	9.9606 inch
Net weight	5800 g		

**Temperatures**

Ambient temperature 5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a1, 6bl, 6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	7d9d08e1-8ede-49b5-a637-5ea27a383bef

**Labelling systems**

Marker type	MultiMark, Shrink-fit sleeves, Label reel	Memory (RAM)	256 MB
System requirements	PC with operating system Windows 7, 8 or 10	Printing method	Thermal transfer
Interface	USB 2.0, Ethernet	Software	M-Print® PRO
Supply voltage	100...240 V AC	Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10, Windows 11
Printing speed	max. 150 mm/s	Print resolution, max.	300 DPI
Operation with rechargeable batteries	No	Included in delivery	THM MultiMark, Manual, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, Software M-Print® PRO, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller

**Classifications**

ETIM 6.0	EC000610	ETIM 7.0	EC000610
ETIM 8.0	EC000610	ETIM 9.0	EC000610
ETIM 10.0	EC000610	ECLASS 9.0	24-32-11-90
ECLASS 9.1	24-32-11-02	ECLASS 10.0	24-32-11-90
ECLASS 11.0	24-32-11-90	ECLASS 12.0	24-32-11-90
ECLASS 13.0	24-32-11-90	ECLASS 14.0	24-32-11-90
ECLASS 15.0	24-32-11-90		