

SDIS SLIM 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749610000
Type	SDIS SLIM 0.6X3.5X100
GTIN (EAN)	4050118896350
Qty.	1 items

SDIS SLIM 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Length	205 mm	Length (inches)	8.0709 inch
Diameter	3.5 mm	Net weight	40 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.6x3.5x100, SlimLine	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	Slotted	Blade length	100 mm

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07	ECLASS 12.0	21-04-04-07
ECLASS 13.0	21-04-04-07	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		