

SDIS 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749810000
Type	SDIS 0.6X3.5X100
GTIN (EAN)	4050118897012
Qty.	1 items

SDIS 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Length	205 mm	Length (inches)	8.0709 inch
Diameter	3.5 mm	Net weight	34 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.6x3.5x100	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	Slotted	Blade length	100 mm
Blade type	B		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07	ECLASS 12.0	21-04-04-07
ECLASS 13.0	21-04-04-07	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		