

SAK Series
STB 30.5 IH/BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	STB 30.5 IH/BL
Order No.	0341200000
Version	SAK Series, Socket
GTIN (EAN)	4008190044077
Qty.	50 pc(s).

Data sheet

**SAK Series
STB 30.5 IH/BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	7.2 mm	Width (inches)	0.283 inch
Depth	31.7 mm	Depth (inches)	1.248 inch
Net weight	2.5 g	Diameter	7.2 mm

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	PA 66	Colour	Blue
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails	Mounting rail	none
---------	------------------------	---------------	------

Additional technical data

Explosion-tested version	No	Type of fixing	Screwed
Type of mounting	Screwed		

Dimensions

Diameter	7.2 mm	Length of thread	7 mm
Plug-in depth	10 mm		

Classifications

ETIM 3.0	EC001134	ETIM 4.0	EC001134
ETIM 5.0	EC001134	ETIM 6.0	EC002848
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-92		

Product information

Instructions for accessories	To safe the test sockets use the SD-blade or bits with pilots!
------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------

Data sheet**SAK Series
STB 30.5 IH/BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
