

Product image

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

General ordering data

Version	Miniature fuse, quick-acting, 0.25 A, G-Si. 5 x 20
Order No.	0430500000
Type	G 20/0.25A/F
GTIN (EAN)	4008 19015399 1
Qty.	10 ST

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.9 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Optical function display	No	Cartridge fuse	G-Si. 5 x 20
Current	0.25 A	Version	Fuse accessories
Colour	Light Grey	Voltage drop	280 mV
Rated breaking capacity	1.5 kA	Melting integral	0.07 A ² s
Characteristics	quick-acting	Power output (@ 1.5 In)	0.3 W

Rating data

Rated voltage	250 V	Rated current	0.25 A
---------------	-------	---------------	--------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ETIM 10.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01
ECLASS 13.0	27-14-20-01	ECLASS 14.0	27-14-20-01
ECLASS 15.0	27-14-20-01		