

Marksman® Iron (120 Watt)



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	SP120
UPC Code	037103474537
Type	Non-temperature Controlled
Wattage	120 W
Temperature Range	900° F
Cord Length	6 ft.
Components Supplied	MTG30
Packaging	Peg Hook/Retail Packaging
Tech. Spec.	Solder Safety Warnings.pdf
Low Res. Image	SP120_100.jpg
High Res. Image	SP120_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Fine quality, heavy-duty iron, 11 3/8"/289mm long
- Ideal for home workshop, repairs, stained glass and hobbies
- Soldering iron rest included
- MTG30 1/2"/13mm diameter replaceable iron-plated copper tip
- Develops 900°F/482°C temperature
- Stainless steel barrel and heat and impact resistant handle
- IMPORTANT: Use only Weller® tips
- UL listed - cUL version available