

## Hot Air Rework Station With Internal Pump, 120 V

◀◀ previous print close next ▶▶



Product Details	
Catalog No.	WHA 900
UPC Code	037103222282
Wattage	650 W
Desoldering Pencil(s)	None
Temperature Range	122Â° F to 1022Â° F
Voltage	120 V / 24 V
Supplied Tip(s)	None
Air Flow Volume	5 l/min - 50 l/min
Pump Type	Turbine
Packaging	Industrial Box / Carton
Literature	<a href="#">550582.pdf</a>
Low Res. Image	<a href="#">WHA900_100.jpg</a>
High Res. Image	<a href="#">WHA900_300.jpg</a>
Operating Ins.	<a href="#">WHA900 USA Manual.pdf</a>
Stock Item	Normal Stock Item

### Package Details (Dimensions)

[Email this Page](#)

### Product Features:

- For reworking SMT components
- Compact design maximizes workspace efficiency
- Controlled output maintains set temp regardless of air flow setting
- Temperature and air flow are controlled independently
- Standby button allows you to power down to low settings when not in use
- Includes a rest support for the hand piece
- Nozzles sold separately