



ARMSTRONG

CRESCENT

Erem



Lufkin

Xcelite

U.S.

Weller

Login

Distributor Login

My Account

Wishlist

Checkout

My Cart (0)

Search



Menu



Home >

REWORK SYSTEM,3 FUNCTION,120V

Catalog Number: WR3000M

0



Availability: In stock

Qty:

1

Add to Cart



Add to Wishlist



Download Images

***** Be the first to review this product



Features

Specifications

Related Products

Accessories

Reviews

Material ID	WR3000M
Channels	3
Wattage	400 W
Temperature Range	200°F to 850°F

Temperature Accuracy	±17°F (±9°C)
Temperature Stability	±4°F (±2°C)
Air Flow Volume	15 l/min
Extraction Rate Maximum	1 l/min, 15 l/min
Vacuum Pressure	.7 bar, 20.7 inHg
Voltage Input	120 V
Voltage Output	24 V
Pump Type	Rotary Vane
Style Type	Rework Stations
Nozzle Type	HAP
Tool Grip Material	PLASTIC
Packaging	No
Package Length	17.91 in
Package Width	14.17 in
Package Height	14.57 in
Package Gross Weight	25.90 lb
UPC	037103224859
Country of Origin	Germany
Foreign Trade Code	8515190000

Recently Viewed Products



WHC-52 HOT AIR TIP
7 0 - 0 1 - 5 2

Add to Cart

Add to Wishlist



Soldering Iron LED, 80
W a t t , 1 2 0 V

Add to Cart

Add to Wishlist



Soldering Iron LED, 40
W a t t , 1 2 0 V

Add to Cart

Add to Wishlist



CHISEL TIP 0.8MM
NTH

Add to Cart

Add to Wishlist



NEEDLE, 15 GA
1/2", 50/PK

Add to Cart

Add to Wishlist

Weller®

weller-na@weller-tools.com
(800) 621-8814

Products
Where to Buy
Technical Support
Resources

Media Center
Companion Brands
About Us
Customer Service

Inventor Connect
Contact Us
Privacy Policy
My Account

Search 

Connect



Merchant
Services

© 2014 Apex Tool Group, LLC. All rights reserved.