





Phillips Stubby SoftFinish® Screwdrivers



SKU	Product	Size Phillips	Blade Length Inch	OAL MM
31135	 SoftFinish® Phillips Stubby Driver #1	#1	1	75
31140	 SoftFinish® Phillips Stubby Driver #2	#2	1	75

Details

Wiha SoftFinish Handle

- > Dual material molded improves comfort and performance.
- > Through ergonomic design the handle allows 40% more torque and less hand fatigue than conventional handles.
- > Handle with roll-off protection feature.


Wiha Screwdriver Tips

- > Wiha tips are precision machined to exact tolerances for a perfect fit every time.
- > Wiha utilizes an exclusive chrome-vanadium-molybdenum tool steel.
- > Through hardened to 60 on the Rockwell C scale.

Wiha Hard Chromtop Plating

- > Provides additional unmatched durability for tips and blade integrity.

Additional Info

RoHS Compliant	Yes
Head Type	 phillips
Handle Grip Types	SoftFinish®
Steel HRC	60
OAL MM	75
OAL Inch	3