

Wiha torque screwdrivers.

Torque interchangeable blades.



2859 Torque slotted interchangeable blade. For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: grey.

Standards: Blade tip DIN ISO 2380-1.

Application: For applications where recommended torque settings are important.

Order-No.	⌀	⌀	⌀	⌀	⌀	max. Nm	⌀
26227	0.25	1.5	4	175	42	0.15	10
26228	0.4	2.0	4	175	42	0.4	10
26151	0.4	2.5	4	175	42	0.4	10
26277	0.5	3.0	4	175	42	0.6	10
26278	0.6	3.5	4	175	42	1.1	10
26279	0.8	4.0	4	175	42	2.5	10



2859 Torque Phillips interchangeable blade. For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: dark blue.

Standards: Blade tip DIN ISO 8764-1.

Application: For applications where recommended torque settings are important.

Order-No.	⊕	⌀	⌀	⌀	⌀	max. Nm	⌀
26199	PH000	4	175	42	0.4		10
26196	PH00	4	175	42	0.4		10
26197	PH0	4	175	42	0.9		10
26058	PH1	4	175	42	3.8		10
27079	PH2	4	175	42	5.5		10



2859 Torque cable key for circular plug connectors. For Wiha torque screwdrivers.

Material: Robust, glass-fibre reinforced plastic combines the high quality hexagonal stainless steel insert with the blade tang of chrome-vanadium-molybdenum steel.

Application: For controlled fastening of circular plug connectors with hexagonal head according to specified torque.

Order-No.	⌀	⌀	⌀	⌀	max. Nm	⌀
36414	8	4	78	218	1	10
36415	9	4	78	218	1	10
38004	11	4	78	218	1.5 NEW	10
36413	1/2"	4	78	218	1.5	10
36416	12	4	78	218	1.5	10
36417	13	4	78	218	1.5	10
36418	14	4	78	218	1.5	10
36419	17	4	78	218	1.5	10
36421	18	4	78	218	1.5	5
36553	19	4	78	218	1.5	5
36422	22	4	90	233	2	5
36423	24	4	90	233	2	5

Torque interchangeable blades.



2859 Torque Pozidriv interchangeable blade. For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: light blue.

Standards: Blade tip DIN ISO 8764-1.

Application: For applications where recommended torque settings are important.

Order-No.	⊕	⌀	⌀	⌀	max. Nm	⌀
26198	PZ0	4	175	42	0.9	10
26148	PZ1	4	175	42	3.8	10
26889	PZ2	4	175	42	5.5	10



2859 Torque hex interchangeable blade. For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: red.

Application: For applications where recommended torque settings are important.

Order-No.	⊕	⌀	⌀	⌀	max. Nm	⌀
26544	1.3	4	175	42	0.4	10
26200	1.5	4	175	42	0.9	10
26060	2.0	4	175	42	1.8	10
26061	2.5	4	175	42	3.8	10
26062	3.0	4	175	42	5.5	10
26063	4.0	4	175	42	8.0	10



2859 Torque ball end hex interchangeable blade. For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: red.

Application: For applications where recommended torque settings are important.
Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	⊕	⌀	⌀	⌀	max. Nm	⌀
26221	1.5	4	175	42	0.4	10
26222	2.0	4	175	42	0.9	10
26223	2.5	4	175	42	2.0	10
26224	3.0	4	175	42	3.8	10
26225	4.0	4	175	42	8.0	10