

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200310028](#)  
**Status:** **Active**  
**Overview:** [Brad Nano-Change \(M8\) Products](#)  
**Description:** Nano-Change (M8) Receptacle, 5 Poles, M8 x 0.5 Mounting Threads, Female (Straight) to 22 AWG Leads, 0.30m (11.81") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Receptacles  
 Series [120031](#)  
 IP Rating IP67  
 NEMA Rating NEMA 6  
 Overview [Brad Nano-Change \(M8\) Products](#)  
 Product Name Nano-Change (M8)  
 Type Single Ended (pigtail)  
 UPC 883906177850

**Physical**

Coupling Type Internal Thread  
 Gender Female  
 Keyway None  
 Length 0.30m  
 Material - Component Nickel-plated Brass  
 Mounting Thread Size M8 x 0.5  
 Orientation Straight  
 Panel Mount Front  
 Poles 5  
 Temperature Range - Operating -25°C to +90°C  
 Wire Size AWG 24  
 Wire/Cable Type Leads

**Electrical**

Current - Maximum per Contact 3.0A  
 Voltage - Maximum 60V AC / 75V DC

**Material Info**

Engineering Number 4R5F30E02C3003

**Reference - Drawing Numbers**

Sales Drawing 4RXF30XXXXXXX3, SD-120090-028

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120031](#) Series