

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200310118](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Receptacle, PG7 Mounting Threads, Female (Straight), PCB Mount, 4 Poles

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120031
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	PCB Mount
UPC	883906178024

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	None
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG7
Net Weight	11.196/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	24
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Material Info

Engineering Number	4R4H400013
--------------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-120090-012
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120031](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION