

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200650200](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 22 AWG, PVC Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120065](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Protocol N/A  
 Region America  
 Type Single Ended  
 UPC 78678824100

**Physical**

Cable Diameter 4.57mm (.180")  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Male-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold over Nickel  
 Orientation Straight to Pigtail  
 Poles 3  
 Temperature Range - Operating -20°C to +105°C  
 Wire Size AWG 22  
 Wire/Cable Type UL 2661

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 803006A09M020

**Reference - Drawing Numbers**

Sales Drawing SD-120065-028



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120065 Series](#)

This document was generated on 09/18/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**