

6

5

4


3

2

1

E

E



FACE VIEW - FEMALE

FACE VIEW - MALE

D

D

1	BROWN	1
2	WHITE	2
3	BLUE	3
4	BLACK	4
5	GRAY	5

MOLEX SAP P/N#	ENGINEERING P/N#	"L" (Meters)	"L" (INCH)	TOLERANCE (INCH)
1200661779	885030KF3M005N	0.5 M	19.68"	+1.75"/-0.00"
1200661751	885030KF3M010N	1.0 M	39.37"	+2.19"/-0.00"
1200661780	885030KF3M015N	1.5 M	59.05"	+2.19"/-0.00"
1200661752	885030KF3M020N	2.0 M	78.74"	+3.50"/-0.00"
1200661781	885030KF3M025N	2.5 M	98.42"	+3.50"/-0.00"
1200661753	885030KF3M030N	3.0 M	118.11"	+3.50"/-0.00"
1200661782	885030KF3M035N	3.5 M	137.79"	+3.50"/-0.00"
1200661754	885030KF3M040N	4.0 M	157.48"	+6.50"/-0.00"
1200661755	885030KF3M050N	5.0 M	196.85"	+6.50"/-0.00"
1200661756	885030KF3M060N	6.0 M	236.22"	+6.50"/-0.00"
1200661757	885030KF3M080N	8.0 M	314.96"	+12.50"/-0.00"
1200661758	885030KF3M100N	10.0 M	393.70"	+12.50"/-0.00"
1200661759	885030KF3M120N	12.0 M	472.44"	+12.50"/-0.00"
1200661760	885030KF3M150N	15.0 M	590.55"	+24.50"/-0.00"
1200661761	885030KF3M200N	20.0 M	787.40"	+24.50"/-0.00"

C

C

B

B

**SPECIFICATIONS:**

COUPLING NUT MATERIAL: ZINC DIECAST WITH  
BLACK ELECTROPHORETIC COATING  
CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY  
INSERT MATERIAL: BLACK NYLON  
OVERMOLD MATERIAL: YELLOW TPE  
O-RING MATERIAL: VITON

CABLE: #18/5 YELLOW TPE  
10 MILLION CYCLE HI-FLEX  
PLTC & FT4 RATED

ASSEMBLY RATING: 250V, 4A

ENVIRONMENTAL: -20°C TO 105°C  
IP67 WHEN MATED

AGENCY: UL LISTED

A

A

A201110637 RELEASE EC NO: WNA2011-0422 DRWN: YOU 2011/02/03 CHKD: LHARTMAN APPR: JFMURPHY 2012/03/20	DESCRIPTION REV 2	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION															
		$\nabla=0$ $\sphericalangle=0$	<table border="1"> <tr><th></th><th>mm</th><th>INCH</th></tr> <tr><td>4 PLACES</td><td>±---</td><td>±---</td></tr> <tr><td>3 PLACES</td><td>±---</td><td>±.005</td></tr> <tr><td>2 PLACES</td><td>±0.13</td><td>±0.10</td></tr> <tr><td>1 PLACE</td><td>±0.25</td><td>±0.020</td></tr> </table>		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±.005	2 PLACES	±0.13	±0.10	1 PLACE	±0.25	±0.020	INCH	3:4	INCH	
			mm	INCH																		
		4 PLACES	±---	±---																		
3 PLACES	±---	±.005																				
2 PLACES	±0.13	±0.10																				
1 PLACE	±0.25	±0.020																				
	ANGULAR ±1/2°	DRAWN BY DATE	TITLE	M12 CORDSET ASSEMBLY 5P MALE/FEMALE #18/5 TPE CABLE MOLEX INCORPORATED																		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	YOU 2011/02/03																				
		CHECKED BY DATE	MATERIAL NO.	SD-120066-041	SHEET NO.																	
		LHARTMAN 2012/02/17	SEE CHART	1 OF 1																		
		APPROVED BY DATE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
		JFMURPHY 2012/03/20																				

6

5

4

3

2

1