

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200668378](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 0.34mm² PUR LS0H Cable, 0.60m (1.97') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120066](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Region Europe
 Type Double Ended
 UPC 78172514602

Physical

Cable Diameter 4.70mm (.185")
 Cable Length 0.60m (1.97')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PUR
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold over Nickel
 Net Weight 61.134/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -25°C to +80°C
 Wire Size AWG N/A
 Wire/Cable Type UL 21198

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 884030H09M006

Reference - Drawing Numbers

Sales Drawing 1200668084-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120066 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION