

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200860474](#)

**Status:** **Active**

**Overview:** [Brad Nano-Change \(M8\) Products](#)

**Description:** Nano-Change (M8) Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 0.25mm<sup>2</sup> PUR/PVC Cable, 5.0m (16.40') Length, PUR Cable Preferred Version in Europe

**Documents:**

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120086</a>
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	<a href="#">Brad Nano-Change (M8) Products</a>
Product Name	Nano-Change (M8)
Region	Europe
Type	Single Ended
UPC	78678897287

**Physical**

Cable Diameter	4.32mm (.170")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	UL 2464

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

**Material Info**

Engineering Number: 403006P02M050

**Reference - Drawing Numbers**

Sales Drawing: SD-120027-002, SD-120086-002-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120086 Series](#)