

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200878348](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 24 AWG, PVC Cable, 0.60m (1.97') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120087
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	78172532309

Physical

Cable Diameter	4.57mm (.180")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	50.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	24
Wire/Cable Type	UL 2464

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V

Material Info

Engineering Number	444030E02M006
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200878240-000
---------------	----------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120087](#) Series