

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210400159](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A - 18mm, 2 Pole Plus Ground Position H6/H12, to 2.0m (6.56') PVC Cable Pigtail, Black Nitrile Gasket, 250V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E218123

General

Product Family Industrial Cordsets
Series [121040](#)
Connector End A Brad mPm DIN A - 18mm
Connector End B Pigtail
IP Rating IP65
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Region America, Europe
Type Single Ended
UPC 883906580711

Physical

Cable Diameter 5.72mm (.225")
Cable Length 2.0m (6.56')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Male-Pigtail
Keyway None
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body Polypropylene
Material - Coupling Nut N/A
Material - Plating Mating Gold over Nickel
Net Weight 153.630/g
Orientation 90° to Pigtail
Poles 2
Temperature Range - Operating -25°C to +75°C
Wire Size AWG N/A
Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 5.0A
Voltage - Maximum 250V

Material Info

Engineering Number E152N3N20011

Reference - Drawing Numbers

Sales Drawing 1210400050-000, E152XXXXXXXXX



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121040 Series](#)