

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130013-0541](#)
Status: **Active**
Overview: Brad® Mini-Change® Connectors
Description: Mini-Change® A-Size Bulkhead Feed-Through, 4 Poles, 7/8-16UN, Nickel Plated Brass, 0.049m (1.94") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Receptacles
 Series [130013](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad® Mini-Change® Connectors](#)
 Product Name Mini-Change®
 Type Bulkhead Feed-Through
 UPC 78678845498

Physical

Coupling Type External Thread
 Gender Male-Female
 Keyway Single
 Length 0.049m
 Material - Component Nickel-plated Brass
 Mounting Thread Size 7/8" - 16 UN-2A
 Orientation Straight
 Panel Mount N/A
 Poles 5
 Temperature Range - Operating -20°C to +60°C
 Wire Size AWG N/A
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 8.0A
 Voltage - Maximum 600V

Material Info

Old Part Number 1R5030

Reference - Drawing Numbers

Sales Drawing SD-130013-012

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130013Series](#)