

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300150109](#)
Status: **Active**
Overview: Brad Mini-Change Connectors
Description: Mini-Change C-Size Receptacle, 19 Poles, 1/2" - 14 NPT Threads, Male (Straight) to Leads, 0.30m (11.81") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	130015
Comments	C-Size (1-1/8" - 16 UN-2A), C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678841464

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.30m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	PG16
Net Weight	90.718/g
Orientation	Straight
Panel Mount	Back, Front
Poles	19
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	18, 22
Wire/Cable Type	N/A

Electrical


Current - Maximum per Contact	2.0A
Voltage - Maximum	300V AC/DC

Material Info

Engineering Number	3R3N36E80C300
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-130015-009
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130015 Series](#)