


12	11	10	9	8	7	6	5	4	3	2	1
PART NO	ENGINEERING NO.	FINISHED LENGTH	C								
1300621009	113030K20M020	2M [6 FT 7 IN]									
1300621153	113030K20M900G	90M [295 FT 3 IN]									
1300621122	113030K20T170E	170M [557 FT 9 IN]									

CABLE LENGTH TOLERANCES
<.3M [1FT]: +19mm-0 [+.75in-0]
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]
.9 - 1.8M [3 - 6FT]: +55.6mm-0 [+2.19in-0]
1.8 - 3.7M [6 - 12FT: +88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]
OVER 30M [100FT] +2% OF FINISHED LENGTH

MALE - FACE VIEW




- NOTES:
- 1. MATERIAL: AS NOTED
 - 2. FINISH: AS NOTED
 - 3. ELECTRICAL:
 - VOLTAGE: 500V PER IEC60664
 - 600V PER UL2237
 - CURRENT: 15A
 - 4. TEMP RATING: -20° TO +90°C
 - 5. PROTECTION: IP67 (WHEN MATED)
 - 6. COUPLING THREAD: 7/8"-16UN
 - 7. UL LISTED FILE: E258922
 - 8. ALL DIMENSIONS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE


11	WARNING LABEL	VINYL	ORANGE/BLACK
10	WRAP LABEL	VINYL	BLACK/YELLOW
9	FRICTION RING	NYLON	NATURAL
8	OVERMOLD	TPE	SEE P/N MATRIX
7	MALE COUPLING NUT	ZINC ALLOY	BLACK E-COAT
6	CONTACT PIN	Cu ALLOY	GOLD PLATED
5	MALE INSERT	TPE	BLACK
4	FEMALE COUPLING NUT	ZINC ALLOY	BLACK E-COAT
3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	FEMALE INSERT	TPE	BLACK
1	CABLE 14AWG TC-ER	TPE JACKET	BLACK
ITEM	COMPONENT	MATERIAL	FINISH

DOCUMENT STATUS	P1	RELEASE DATE	2021/05/13	00:30:14
-----------------	----	--------------	------------	----------

FINISHED LENGTH



FEMALE - FACE VIEW



PART NO. MATRIX
113030K20M020E

FINISHED LENGTH
M005= 0.5 METER
M010= 1 METER
M100= 10 METER
T100= 100 FEET
T150= 150 FEET

MOLD COLOR:
BLANK= GRAY (STD)
E= RED
G= BLACK

1	GRN/YEL	1
2	BLACK	2
3	WHITE	3

WIRING DIAGRAM

FUNCTIONAL SYMBOLS FA=0 FE=0 FP=0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ITEM 2, 5 & 8 WERE PVC. ADDED CABLE DIA. MODIFIED PART NUMBER CHART				molex MINI-CHANGE CORDSET, A-SIZE, 3 POLE, MALE-FEMALE, STRAIGHT, SINGLE KEY, #14 AWG						
	INCH/MM		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
		mm		INCH	EC NO: 663067				PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-130062-021 DOC TYPE DOC PART REVISION PSD 001 C						
	4 PLACES	±----		±----	DRWN: ABENJAMINLW 2020/10/28										
	3 PLACES	±----		±----	CHK'D: RSTONE 2021/05/06										
	2 PLACES	±----		±----	APPR: BWOODMAN 2021/05/13										
	1 PLACE	±----		±----	INITIAL REVISION:										
	0 PLACES	±----		±----	DRWN: GGUSTAFS 2014/07/09										
ANGULAR TOL ± ---- °				APPR: BWOODMAN 2014/09/04											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		130062		SEE CHART		GENERAL MARKET		1 OF 1	