

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300830224](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/3 SOW, 9.14m (30.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR29921
 UL E22769

General

Product Family Electric Reels
 Series [130083](#)
 Cable Length N/A
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag., Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
 Depth 0.34m (13.50")
 Duty Industrial
 Enclosure Rating NEMA 4
 Exclude SD Check Yes
 Height 0.37m (14.50")
 NEMA Configuration N/A
 Overview [Reels - Woodhead](#)
 Product Literature Order No 987650-8062
 Product Name POW-R-MITE
 Type Cable Reel
 UPC 78678879224
 Width 244.35mm (9.620")

Physical

Cable Movement Ratchet Lock
 Cord Length 9.14m (30.0')
 Drum Lock Ratchet
 Guide Arm 5° increments over 270° Arc
 Material - Coating Powder Coating
 Material - Housing Cast Aluminum
 Mounting Style Rigid
 Net Weight 16329.312/g
 Number of Conductors 3
 Packaging Type Carton
 Primary Cord/Cable Entry 1" NPT
 Retraction Weight 1.8kg (4.0 lb)
 Wire Size AWG 16

Electrical

Bulb Included N/A
 Cord Type 16/3 SOW
 Current - Maximum per Contact 9.0A
 GFCI No
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch N/A



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

China RoHS

Search Parts in this Series

[130083 Series](#)

Voltage - Maximum

600V

Material Info

Engineering Number

9224

This document was generated on 09/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION