

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300940255

Status:

Active

Overview:

Support Grips

Description:

Standard Duty Support Grip, Offset Eye, Closed Mesh, Single Weave, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 435.45kg (960 lbs)

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

LR32159

General

Product Family

Series

Exclude SD Check

Eye Type

O-Ring

Overview

Product Literature Order No

Product Name

Type

UPC

Cable Grips

130094

Yes

Offset

N/A

Support Grips

987650-8065

Standard Duty

Support Grip

78678835062

Physical

Approximate Break Strength

Bale Length

Body Style

Cable Diameter

Color - Grommet

Gender

Material - Body

Material - Grip

Mesh Length

Number of Holes

Thread Size

435.45kg (960 lbs)

0.102m (4.00")

Straight

19.05-25.15mm (.750-.990")

N/A

N/A

N/A

Non-magnetic Tin Bronze Wire

0.356m (14.00")

N/A

N/A

Material Info

Engineering Number

35062



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130094 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION