

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300950149

Status:

Active

Overview:

Pulling Grips

Description:

Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh
Length 0.419m (16.50"), Approximate Break Strength 2630.84kg (5800 lbs)



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR32159
General	
Product Family	Cable Grips
Series	130095
Exclude SD Check	Yes
Eye Type	Flexible
O-Ring	N/A
Overview	Pulling Grips
Product Literature Order No	987650-8066
Product Name	Light Duty
Type	Pulling Grip
UPC	78678835904
Physical	
Approximate Break Strength	2630.84kg (5800 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	25.40-31.50mm (1.000-1.240")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.419m (16.50")
Number of Holes	N/A
Thread Size	N/A
Material Info	
Engineering Number	35904
Reference - Drawing Numbers	
Sales Drawing	SD-130095-101

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION