

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950190](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Long Mesh Length 1.219m (48.00"), Approximate Break Strength 8799.69kg (19400 lbs)

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Exclude SD Check Yes
 Eye Type Flexible
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Literature Order No 987650-8066
 Product Name Medium Duty
 Type Pulling Grip
 UPC 78678835962

Physical

Approximate Break Strength 8799.69kg (19400 lbs)
 Bale Length N/A
 Body Style Straight
 Cable Diameter 38.10-50.55mm (1.500-1.990")
 Color - Grommet N/A
 Gender N/A
 Material - Body N/A
 Material - Grip Galvanized Steel
 Mesh Length 1.219m (48.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35962

Reference - Drawing Numbers

Sales Drawing SD-130095-105



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130095 Series](#)