

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950227](#)  
**Status:** **Active**  
**Overview:** Support Grips  
**Description:** Heavy Duty Wire Mesh Slack Grip Cable, Closed Mesh, Double Weave, Offset Eye, Medium Mesh Length 0.406m (16.00"), Approximate Break Strength 1905.09kg (4200 lbs)

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130095](#)  
 Exclude SD Check Yes  
 Eye Type Offset  
 O-Ring N/A  
 Overview [Support Grips](#)  
 Product Literature Order No 987650-8066  
 Product Name Heavy Duty  
 Type Pulling Grip  
 UPC 78678836102

**Physical**

Approximate Break Strength 1905.09kg (4200 lbs)  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 25.40-31.50mm (1.000-1.240")  
 Color - Grommet N/A  
 Gender N/A  
 Material - Body N/A  
 Material - Grip Galvanized Steel  
 Mesh Length 0.406m (16.00")  
 Number of Holes N/A  
 Thread Size N/A

**Material Info**

Engineering Number 36102

**Reference - Drawing Numbers**

Sales Drawing SD-130095-113



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130095 Series](#)