

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300960073](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Liquid-Tight Grip Strain Relief for Non-Metallic Type A Flexible Conduit, 1" NPT, Straight Male, Mesh Length 0.305m (12.00")

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E61303

General

| | |
|-----------------------------|--|
| Product Family | Cable Grips |
| Series | 130096 |
| Exclude SD Check | Yes |
| Eye Type | N/A |
| NEMA Rating | NEMA 4 |
| O-Ring | No |
| Overview | Strain-Relief Cord Grips |
| Product Literature Order No | 987651-6081 |
| Product Name | Liquid-Tight |
| Type | Strain Relief Grip |
| UPC | 78678837103 |
| Use With | MAX-LOC Lock Nut 1" NPT 1300990145 , MAX-LOC Gasket Sealing Ring 1" NPT 1300990151 , MAX-LOC O-Ring, 1" NPT 1301800334 |

Physical

| | |
|----------------------------|-----------------------------------|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | N/A |
| Color - Grommet | N/A |
| Gender | Male |
| Material - Body | Malleable Iron, Zinc Plated Steel |
| Material - Grip | Stainless Steel |
| Mesh Length | 0.305m (12.00") |
| Number of Holes | N/A |
| Thread Size | 1" NPT |

Material Info

Engineering Number 37103

Reference - Drawing Numbers

Sales Drawing SD-130096-104



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130096 Series](#)