

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970168](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Deluxe Cord Grips Strain Relief, 3/4" NPT, Grip Body Size F3, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625")

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130097](#)
 Exclude SD Check Yes
 Eye Type N/A
 Hazardous Locations Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
 NEMA Rating NEMA 4
 O-Ring N/A
 Overview [Strain-Relief Cord Grips](#)
 Product Literature Order No 987651-6081
 Product Name Deluxe Cord
 Type Strain Relief Grip
 UPC 78678836261
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

Physical

Approximate Break Strength N/A
 Bale Length 0.089m (3.50")
 Body Style Straight
 Cable Diameter 12.70-15.88mm (.500-.625")
 Color - Grommet N/A
 Gender Male
 Material - Body Aluminum
 Material - Grip Stainless Steel
 Mesh Length 0.178m (7.00")
 Number of Holes N/A
 Thread Size 3/4" NPT

Material Info

Engineering Number 36261

Reference - Drawing Numbers

Sales Drawing SD-130097-103



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130097 Series](#)