

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970336](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 17.45-20.62mm (.687-.812"), Stainless Steel Mesh

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family	Cable Grips
Series	130097
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678837148
Use With	MAX-LOC Lock Nut 1" NPT 1300990145 , MAX-LOC Gasket Sealing Ring 1" NPT 1300990151 , MAX-LOC O-Ring, 1" NPT 1301800334

Physical


Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	17.45-20.62mm (.687-.812")
Color - Grommet	N/A
Gender	Male
Material - Body	Stainless Steel
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
Thread Size	1" NPT

Material Info

Engineering Number 5554MSS

Reference - Drawing Numbers

Sales Drawing SD-130097-102



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130097 Series](#)