

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300980149](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, 90° Angle Male with O-Ring, Cable Diameter 15.88-19.05mm (.625-.750")

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR32159  
 UL      E76954

**General**

Product Family      Cable Grips  
 Series      [130098](#)  
 Exclude SD Check      Yes  
 Eye Type      N/A  
 NEMA Rating      NEMA 6P  
 O-Ring      Yes  
 Overview      [Strain-Relief Cord Grips](#)  
 Product Literature Order No      987651-6081  
 Product Name      MAX-LOC  
 Type      Strain Relief Grip  
 UPC      78678818932  
 Use With      MAX-LOC Lock Nut 1" NPT [1300990145](#)

**Physical**

Approximate Break Strength      N/A  
 Bale Length      N/A  
 Body Style      90° Angle  
 Cable Diameter      15.88-19.05mm (.625-.750")  
 Color - Grommet      N/A  
 Gender      Male  
 Material - Body      Nylon  
 Material - Grip      N/A  
 Mesh Length      N/A  
 Number of Holes      1  
 Thread Size      1" NPT

**Material Info**

Engineering Number      5553W



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130098](#) Series