

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980168](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male with O-Ring, Cable Diameter 19.05-25.40mm (.750-1.000"), Polyester

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130098](#)
Exclude SD Check Yes
Eye Type N/A
NEMA Rating NEMA 6P
O-Ring Yes
Overview [Strain-Relief Cord Grips](#)
Product Literature Order No 987651-6081
Product Name MAX-LOC
Type Strain Relief Grip
UPC 78678855603
Use With MAX-LOC Lock Nut 1" NPT [1300990145](#)

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter 19.05-25.40mm (.750-1.000")
Color - Grommet N/A
Gender Male
Material - Body PBT
Material - Grip N/A
Mesh Length N/A
Number of Holes 1
Thread Size 1" NPT

Material Info

Engineering Number 5560WBLK



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130098 Series](#)