

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300980192

Status:

Active

Overview:

Strain-Relief Cord Grips

Description:

MAX-LOC Strain Relief Cord-Sealing Grip for UF Cable, 3/4" NPT, Straight Male Cable Diameter 5.54x16.26mm (.218x.640") Oval



Series image - Reference only

Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR32159
UL	E76954
General	
Product Family	Cable Grips
Series	130098
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872147
Use With	3/4" NPT MAX-LOC Lock Nut 1300990144 , 3/4" NPT MAX-LOC Gasket Sealing Ring 1300990150 , 3/4" NPT MAX-LOC O-Ring 1301800333
Physical	
Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	5.54x16.26mm (.218x.640") Oval
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
Thread Size	3/4" NPT
Material Info	
Engineering Number	5586

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION