

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990171](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC/Watertite Cord Grips, 3/4" NPT, Straight Male, Body Size F3, Cable Diameter 11.10-14.27mm (.437-.562")

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Grips
Series	130099
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	N/A
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC, Watertite
Type	Strain Relief Grip
UPC	78678856334
Use With	3/4" NPT MAX-LOC Lock Nut 1300990144 , 3/4" NPT MAX-LOC Gasket Sealing Ring 1300990150 , 3/4" NPT MAX-LOC O-Ring 1301800333

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	11.10-14.27mm (.437-.562")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Net Weight	44.100/g
Number of Holes	1
Thread Size	3/4" NPT

Material Info

Engineering Number 5633M

Reference - Drawing Numbers

Sales Drawing SD-130099-007



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130099 Series](#)