

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301080167](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway Twin Tube 64W Fluorescent Work Light with 16/3 SJOW Feed Thru 1.22m (4.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

UL      E174254

**General**

Product Family      Portable Lighting  
 Series      [130108](#)  
 Exclude SD Check      Yes  
 NEMA Configuration      NEMA 5-15  
 Outlet      Feed-Through  
 Overview      [Wide-Area Lighting Products](#)  
 Product Literature Order No      987650-8054  
 Product Name      Super-Safeway  
 Type      Wide Area Lamps  
 UPC      78678867152

**Physical**

Cord Length - Primary      1.22m (4.0')  
 Cord Length - Secondary      0.152m (6.00" )  
 Depth      190.75mm (7.510")  
 Duty      Industrial  
 Guard Included      No  
 Guard Type      N/A  
 Height      82.55mm (3.250")  
 Length      1.39m (54.620")  
 Material - Globe      Butyrate  
 Material - Guard      Nitrile Rubber 80 Shore A  
 Mounting Style      Adjustable Brackets  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Fluorescent  
 Cord Type - Primary      16/3 SJOW  
 Lamp Type      F32/T8  
 Lamp Wattage - Maximum      64W  
 Lumens      5700  
 On/Off Switch      No  
 Voltage (Fixture) - Maximum      120VAC 60 HZ

**Material Info**

Engineering Number      1352



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130108](#) Series