

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370185](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, Cord Clamp, with Cover Plates for (2) Single 20/30A Locking Receptacles Not Included

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating N/A
 Exclude SD Check Yes
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type Single
 Type Multiple Outlet Box
 UPC 78678875042

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
 Cord Grip Body Size Double C-Clamp
 Cord Length N/A
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 1 - Customer Supplied
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact Per Cust. Supplied Receptacle
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA L5-20
 Voltage - Maximum Per Cust. Supplied Receptacle

Material Info

Engineering Number 3083



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)