

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470038](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Connector with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V, Cord Grip Body Size F4

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family [Wiring Devices](#)
 Series [130147](#)
 Exclude SD Check Yes
 IP Rating IP67
 NEMA Configuration Non-NEMA
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-8067
 Product Name Watertite
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678871391

Physical

Cord Grip Body Size F4 1"
 Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade Yes
 Net Weight 545.671/g
 Poles 4-pole/4-wire

Electrical


Cord Type N/A
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 208V

Material Info

Engineering Number 27W09

Reference - Drawing Numbers

Sales Drawing 1301470038-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)