

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470162](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Male Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L17-30 600, 3ø

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-----------------------------|---|
| Product Family | Wiring Devices |
| Series | 130147 |
| Exclude SD Check | Yes |
| IP Rating | IP67 |
| NEMA Configuration | NEMA L17-30 |
| Overview | Watertite Wet-Location Wiring Solutions |
| Product Literature Order No | 987650-8067 |
| Product Name | Watertite |
| Receptacle Type | N/A |
| Specialty | N/A |
| Type | Inlet |
| UPC | 78678871468 |

Physical

| | |
|---------------|---------------|
| Flange | No |
| Flip Lid | Yes |
| Gender | Male |
| Length | N/A |
| Locking Blade | Yes |
| Net Weight | 337.472/g |
| Poles | 3-pole/4-wire |

Electrical

| | |
|-------------------------------|---------|
| Cord Type | N/A |
| Current - Maximum per Contact | 30.0A |
| GFCI | No |
| Lighted Connector | No |
| Voltage - Maximum | 3Ø 600V |

Material Info

| | |
|--------------------|-------|
| Engineering Number | 68W77 |
|--------------------|-------|

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 1301470162-000 |
|---------------|----------------|



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)