

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301500059](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** 20 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 2 Pole/3 Wire, 250V, Blue

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E145923

**General**

Product Family Wiring Devices  
 Series [130150](#)  
 Comments IEC Configuration 309-1/309-2, IEC Configuration 309-1/309-2  
 Exclude SD Check Yes  
 IP Rating IP67  
 NEMA Configuration N/A  
 Overview [Watertite Wet-Location Wiring Solutions](#)  
 Product Name Watertite  
 Receptacle Type Single  
 Specialty Pin and Sleeve  
 Type Receptacle  
 UPC 78678861337

**Physical**

Flange Yes  
 Flip Lid Yes  
 Gender Female  
 Length N/A  
 Locking Blade Yes  
 Poles 2-pole/3-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 250V

**Material Info**

Engineering Number 320R6W



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130150 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**