

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130098-0217](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC® Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 4.75-6.35mm (.187-.250")

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR32159  
 UL                        E76954

**General**

Product Family	Cable Grips
Series	<a href="#">130098</a>
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	<a href="#">Strain-Relief Cord Grips</a>
Product Literature Order No	987650-8064
Product Name	MAX-LOC®
Type	Strain Relief Grip
UPC	78678856210
Use With	3/4" NPT MAX-LOC® Lock Nut <a href="#">130099-0144</a> , 3/4" NPT MAX-LOC® Gasket Sealing Ring <a href="#">130099-0150</a> , 3/4" NPT MAX-LOC® O-Ring <a href="#">130180-0333</a>
Woodhead	Yes

**Physical**

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	4.75-6.35mm (.187-.250")
Color - Grommet	Orange
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
Thread Size	3/4" NPT

**Material Info**

Old Part Number                      5621



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Not Reviewed**  
**Low-Halogen Status Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130098Series](#)